

CAT. N° 0 039 71



SELF-PROTECTED SPD - FOR SECONDARY DISTRIBUTION BOARD - T2 -IMAX 12 KA/POLE -1P+N LEFT

Pack (number of units)	1
Volume (dm ³)	0,369
Weight (g)	159,00

Product characteristics

Protection for secondary distribution boards

- Protection of sensitive equipment.
- With plug-in modules and status indicators:
 - Green: SPD operational
 - Red: plug-in module need to be replaced
- In: 10 kA/pole - Uc: 275 V~
- Earthing systems: TT, TNS.
- Cat. No. 0 039 71: SPD with Y connection both incoming and outgoing terminals at the top of the SPD, providing better protection against overvoltages

T2 self protected SPDs - I_{max} 12 kA/pole

- 1P+N and 3P+N: L-N and N-PE protection modes (common and differential modes), the N pole being protected by encapsulated spark gaps. Also called 1+1 and 3+1.
- Number of poles : 1P+N
- Neutral position : Left
- Integrated protection : I_{sc} ≤ 10 kA
- Number of modules : 2

General characteristics

Class II (T2) low voltage SPDs with integrated protection

- SPDs with integrated protection against overload currents and short-circuit currents
- SPDs compliant with EN/IEC 61643-11 standards
- For 230/400 VA power networks (50/60 Hz)

Documentation

Catalogue pages & additional information

- [Technical page \(p.074-075\)](#)
- [Description page \(p.078\)](#)
- [Technical page \(p.079\)](#)
- [Technical page \(p.080-081\)](#)
- [Dimensions of din-rail equipment](#)

Installation & technical data

- [F00359EN/04](#)

Installation instructions & related documents

- [0064GY205/07](#)

Agreements & certificates of conformity

- [OC / CB - FR_705325](#)