

CAT. N° 6 174 68

**SHAVER SOCKET BELANKO COLOURS - 2 GANG - BROWN**

Pack (number of units)	1
Volume (dm <sup>3</sup> )	2,256
Weight (g)	698,00

**Product characteristics****Shaver sockets**

- Conform to BS 61558
- 115/230 V - 20 VA - 50/60Hz
- Surface or flush-mounting, back box to be min. 47 mm deep

**2 gang**

- Brown

**General characteristics****Belanko™ colours - hotel equipment**

- Material: Thermoplastic with paint satin finish
- Dimensions: 86 x 86 x 9.5 mm (1 gang) / 86 x 146 x 9.5 mm (2 gang)
- Supplied with 2 screws M3.5 for BS boxes

**Documentation****Catalogue pages & additional information**

- [Description page \(p.556\)](#)

**Installation & technical data**

- [F01055EN/01](#)