

CAT. N° 8 322 90



## SHAVER SOCKET SYNERGY - 230-120 V - 50/60 HZ - SLEEK DESIGN POLISHED STAINLESS STEEL

Pack (number of units)	O/R
Volume (dm <sup>3</sup> )	O/R
Weight (g)	O/R

### Product characteristics

#### Shaver sockets

- Conform to BS EN 61558-2-5
- Suitable for use with European, British, American and Australian 2 pin plugs
- Rating: 20 VA
- IP 24
- Screwless live and neutral terminals
- For flush-mounting, back box to be min. 45 mm deep
- Supplied with 2 gang side extension (3 mm thick) in case of extra wiring space needed
- Nominal plate dimensions: 146 x 86 mm

#### 230 V / 120 V - 50/60 Hz

- Polished stainless steel

### General characteristics

#### Synergy™ - hotel equipment - Sleek Design

- Sleek design
- BSS: Plates made of austenitic Stainless Steel - non-magnetic - grade 304 L
- PSS: Plates made of Stainless Steel + rust resistance
- GG: Plates made of Stainless Steel + rust resistance
- Terminal screws captive and backed off ready for cabling - large angled terminal entries
- Compact mechanism for maximum wiring space

### Documentation



#### Catalogue pages & additional information

- [Description page \(p.594\)](#)



#### Agreements & certificates of conformity

- [OC / CB - FR\\_701616](#)