

CAT. N° 8 334 78



## SINGLE POLE BRITISH STANDARD SOCKET + USB CHARGER SYNERGY - 1 GANG SWITCHED - 13 A 250 V~ - AUTHENTIC GLOSSY GOLD

|                           |        |
|---------------------------|--------|
| Pack (number of units)    | 1      |
| Volume (dm <sup>3</sup> ) | 0,462  |
| Weight (g)                | 162,00 |

### Product characteristics

#### Single pole socket outlets 13 A - 250 V~ with USB charger

- Conform to BS 1363-2
- USB charger conform to IEC 60950-1

#### 1 gang switched

- USB Type-A 2.4 A - 5 VDC - 12 W
- Consumption in passive mode less than 0.08 W
- Glossy gold

### General characteristics

#### Synergy™ - British standard socket outlets - Authentic

- Slim front plate:
  - BSS: Plates made of austenitic Stainless Steel - non-magnetic - grade 304 L
  - PSS: Plates made of Stainless Steel + rust resistance
  - GG: Plates made of Stainless Steel + rust resistance
- Terminal screws captive and backed off ready for cabling - large angled terminal entries
- Compact mechanism for maximum wiring space

### Documentation

#### Catalogue pages & additional information

- [Description page \(p.587\)](#)

#### Agreements & certificates of conformity

- [OC / CB - C-63 SE-88179M2](#)

#### Installation & technical data

- [F02762EN-00](#)