

REF . 8 322 07

**SINGLE POLE PUSH SWITCH SYNERGY - 10 A 250 V~
SLEEK DESIGN POLISHED STAINLESS STEEL**

Emballage (nombre number of units)	O/R
Volume (dm ³)	O/R
Poids (g)	O/R

Caractéristiques du produit**Single pole push switches 10A- 250 V~**

- Conform to BS EN 60669-1
- For flush-mounting, back box to be min. 35 mm deep
- Nominal plate dimensions: 86 x 86 mm

1 gang - 2-way push switches

- Polished stainless steel

Caractéristiques générales**Synergy™ - single pole switches and dimmers -
Sleek Design**

- Sleek design
- BSS: Plates made of austenitic Stainless Steel - non-magnetic - grade 304 L
- PSS: Plates made of Stainless Steel + rust resistance
- GG: Plates made of Stainless Steel + rust resistance
- Terminal screws captive and backed off ready for cabling - large angled terminal entries
- Compact mechanism for maximum wiring space

Documentation associée**Catalogue pages & additional information**

- [Description page \(p.590\)](#)

**Agreements & certificates of conformity**

- [ASTA - 781](#)
- [QC / CB - FR 686293A/A1](#)

**Installation & technical data**

- [F02255EN-00](#)