

CAT. N° 7 300 89

**SOCKET OUTLET SYNERGY - 1 GANG SWITCHED - 15 A  
250 V~ - WHITE**

Pack (number of units)	10
Volume (dm <sup>3</sup> )	4,055
Weight (g)	1 089,00

**Product characteristics****Socket outlets 15 A - 250 V~**

- Conform to BS 546
- Patented 3 pin safety shutter mechanism
- For flush-mounting, back box to be min. 35 mm deep
- Nominal plate dimensions: 86 x 86 mm
- 1 gang - switched, single pole

**General characteristics****Synergy™ - British standard socket outlets - white**

- Front plates: white thermoset
- Terminal screws captive and backed off ready for cabling - large angled terminal entries
- Compact mechanism for maximised wiring space
- Supplied with faceplate screw caps

**Documentation****Catalogue pages & additional information**

- [Description page \(p.582\)](#)

**Installation & technical data**

- [F00164EN-00](#)