

CAT. N° 7 338 65



## SOCKET OUTLET SYNERGY - 1 GANG UNSWITCHED - 13 A 250 V~ - METALCLAD

Pack (number of units)	5
Volume (dm <sup>3</sup> )	2,955
Weight (g)	1 689,00

### Product characteristics

#### Socket outlets 13 A - 250 V~

- Conform to BS 1363 - Part 2: 1995
- With safety shutter mechanism
- Flush-mounting back box: min. 25 mm deep
- 1 gang – unswitched
- Nominal plate dimensions: 86 x 86 mm

### General characteristics

#### Synergy™ - British standard socket outlets, RCD sockets and fused connection units - Metalclad

- Front plates: grey epoxy coated steel
- Terminal screws captive and backed off ready for cabling - large angled terminal entries
- Supplied complete with close fit 43 mm deep surface-mounting back box

### Documentation

#### Catalogue pages & additional information

- [Description page \(p.599\)](#)

#### Agreements & certificates of conformity

- [ASTA - 780](#)

#### Installation & technical data

- [F02494EN/00](#)