

CAT. N° 7 300 83



## SOCKET OUTLET SYNERGY - EURO-US STANDARD - 1 GANG UNSWITCHED + 1 WAY SWITCH - WHITE

Pack (number of units)	10
Volume (dm <sup>3</sup> )	4,055
Weight (g)	1 162,00

### Product characteristics

#### Euro - US standard socket outlets 16 A - 250 V~

- For flush-mounting, back box to be min. 25 mm deep
- Nominal plate dimensions: 86 x 86 mm
- 1 gang - unswitched + 10 AX 1 way switch

### General characteristics

#### Synergy™ - Euro-US socket outlets and shaver socket - white

- Front plates: white thermoset
- Terminal screws captive and backed off ready for cabling - large angled terminal entries
- Compact mechanism for maximised wiring space
- Supplied with faceplate screw caps

### Documentation

#### Catalogue pages & additional information

- [Description page \(p.583\)](#)

#### Installation & technical data

- [F00356EN-00](#)