

CAT. N° 0 405 80

**SOUNDER - IP42 - IK07 - 90 DB - 12/24/48 V= - WHITE**


Pack (number of units)	1
Volume (dm <sup>3</sup> )	1,135
Weight (g)	244,00

**Product characteristics****Sounders**

- Conform to EN 54-3 standard and CE CPR approved
- IP 42 - IK 07
- Surface-mounting
- Sound level: 90 dB at 2 meters - NF S 32-001 sound
- Voltage range: 10 - 58 V
- Average consumption: 12 V DC 5 mA
- 24 V DC 9 mA
- 48 VDC 13 mA

**General characteristics**

**Sounders, sounder beacons, bells, electromagnetic door holder and safety electrical power supplies**

**Documentation** **Catalogue pages & additional information**

- [Description page \(p.697\)](#)

 **Agreements & certificates of conformity**

- [NFSSI Composant - DS 029 A2](#)

 **Installation instructions & related documents**

- [LE02619AB](#)

 **Environmental product profile**

- [Environnemental product sheet n°4 E0027B-FR](#)
- [Environnemental product sheet n°4 E4027A-FR](#)