

CAT. N° 0 262 49



## SPREADERS - FOR DPX/DPX-IS 630 - REAR TERMINALS INCOMING/OUTGOING - 4P

|                           |          |
|---------------------------|----------|
| Pack (number of units)    | 1        |
| Volume (dm <sup>3</sup> ) | 1,32     |
| Weight (g)                | 1 027,00 |

### Product characteristics

#### Accessories

##### Spreaders

- 4P
- Set of incoming or outgoing spreaders

### General characteristics

#### DPX™-IS 630 isolating switches - 400 to 630 A

- Isolating switches for on-load circuit breaking by visible isolation and positive action of the contacts
- Padlock integrated in the handle
- Supplied with terminal shields, and cage terminals
- Conform to IEC 60947-3
- Category of use AC 23 A
- Accept electrical auxiliaries
- Can be mounted on plate in XL<sup>3</sup> enclosures

### Documentation



#### Catalogue pages & additional information

- [Description page \(p.131\)](#)
- [Technical page \(p.132\)](#)
- [Technical page \(p.133\)](#)
- [Description page \(p.149\)](#)
- [Description page \(p.168\)](#)
- [Technical page \(p.170\)](#)
- [DRXTM 630 adjustable](#)
- [DPX<sup>3</sup> 160/250/630 & 1600](#)
- [DPX<sup>3</sup> 630](#)
- [DPXTM-IS 630 isolating switches](#)