

CAT. N° 6 614 52



STANDARD LED EMERGENCY LUMINAIRE TWINSPOT - NON AUTOTEST - 2 X 750 LM - 1H

Pack (number of units)	1
Volume (dm ³)	14,07
Weight (g)	3 481,00

Product characteristics

Standard LED spotlight luminaires - Non-Maintained (NM)

- 2 x 750 lm – 1h

General characteristics

LED Twinspot emergency lighting luminaires

- High performance LED non maintained emergency lighting luminaires
- Certified to IEC and EN 60598-2-22 standards
- High power LEDs spotlights with optimized lighting distribution
- Low consumption electronic switching power supply
- High capacity terminals: 2 x 2.5 mm² - IP 55 - IK 07
- Duration: 1, 2 and 3 hours. Ni-Cd batteries. Recharge time: 24h
- Green charge indicator with high luminosity LED, to improve visibility from the floor when high installation
- Power supply: 230 V~ ± 10% - 50/60 Hz. Class II
- Rest mode with remote control device Cat.No 0 039 01 to avoid battery discharge in case of voluntary power cut
- Surface mounting installation with 4 wall-mounting lugs (Cat.No 0 358 02, supplied) or 4 screws (not supplied)

Documentation



Catalogue pages & additional information

- [Selection chart \(p.679\)](#)
- [Description page \(p.688\)](#)
- [Selection chart \(p.691\)](#)
- [Self-contained emergency lighting luminaires](#)



Agreements & certificates of conformity

- [OC / CB - FR_703823](#)
- [ENEC - ENEC_1075](#)



Installation instructions & related documents

- [LE08274AC](#)