

CAT. N° 6 611 90

**STANDARD LUMINAIRES U34 LED - 3H DURATION WITH
OPAL DIFFUSER - 200 LM**

Pack (number of units)	1
Volume (dm ³)	2,745
Weight (g)	937,00

Product characteristics**Standard luminaires - Maintained/Non-maintained (M/NM)**

- Standard luminaires incorporate an external manual lamp test with testing tool Cat.No 6 612 99

1 h duration with transparent diffuser

- 200 lm - 3h (LEDs)

General characteristics**U34LED environment friendly - indoor self-contained
emergency lighting luminaires LED**

- LED Maintained/Non-maintained units
- High power LEDs with specially designed lenses optimizing the lighting distribution
- IP 42 - IK 07 - Class II
- Power supply: 230 V ± 10% - 50/60 Hz
- Very low consumption switching power supply - Fully recyclable after removing
- Environment friendly Ni-MH batteries
- Removable plug-in plate to ease installation and maintenance
- Automatic terminals with high capacity: 2 x 2.5 mm²
- Charge monitor with a green LED
- Can be equipped with metallic protection grids Cat.Nos 0 626 92/93

Documentation **Catalogue pages & additional information**

- [Selection chart \(p.678\)](#)
- [Description page \(p.683\)](#)
- [Technical page \(p.684\)](#)
- [Selection chart \(p.691\)](#)
- [Self-contained emergency lighting luminaires](#)

 **Agreements & certificates of conformity**

- [QC / CB - 690885](#)

 **Installation instructions & related documents**

- [LE04859AB](#)