

CAT. N° 6 647 99



SURFACE MOUNTING BOX NILOÉ™ - 2 GANG - WHITE

Pack (number of units)	5
Volume (dm ³)	4,047
Weight (g)	465,00

Product characteristics

Surface-mounting boxes

- Can be used horizontally or vertically
- DL PLUS input 20 x 15.5 mm, 32 x 12.5mm, 40 x 20 mm and Ø20 tube

2-gang

- Dimensions: 159.5 x 88.5 mm - height 40 mm
- White

General characteristics

Nilolé™ - surface-mounting boxes, protection cover and special plates

Documentation

Catalogue pages & additional information

- [Description page \(p.539\)](#)

Agreements & certificates of conformity

- NF - 677930
- NF - 677924
- CEBEC - 18687
- NF - 677866
- OC / CB - 610789B/M3
- OC / CB - 686066E
- CEBEC - 18685
- OC / CB - FR_705448/A1
- NF - NF012_1877/A1
- OC / CB - FR_706571
- OC / CB - 677867
- CEBEC - 18686
- NF - 686066A
- NF - NF012_2029
- OC / CB - FR_675842/M1
- VDE - 40034171
- OC / CB - 675833
- OC / CB - FR_705601
- OC / CB - 677932