

CAT. N° 8 332 51

**TELEPHONE SOCKET SYNERGY - UK SECONDARY - AUTHENTIC POLISHED STAINLESS STEEL**

Pack (number of units)	1
Volume (dm ³)	0,462
Weight (g)	117,00

Product characteristics**Telephone sockets**

- For flush-mounting, back box to be min. 35 mm deep
- Nominal plate dimensions: 86 x 86 mm

UK secondary

- Polished stainless steel

General characteristics**Synergy™ - telephone, data sockets and television sockets - Authentic**

- Slim front plate:
 - BSS: Plates made of austenitic Stainless Steel - non-magnetic - grade 304 L
 - PSS: Plates made of Stainless Steel + rust resistance
 - GG: Plates made of Stainless Steel + rust resistance
- Terminal screws captive and backed off ready for cabling - large angled terminal entries
- Compact mechanism for maximum wiring space

Documentation**Catalogue pages & additional information**

- [Description page \(p.586\)](#)