

CAT. N° 0 372 46



## TERMINAL BLOCK VIKING 3 - SPRING - 1 CONNECT - 4 WIRES - PITCH 5 - GREY

|                           |        |
|---------------------------|--------|
| Pack (number of units)    | 60     |
| Volume (dm <sup>3</sup> ) | 1,221  |
| Weight (g)                | 661,00 |

### Product characteristics

#### Connecting

- Grey for standard circuit, blue for neutral conductor, orange for circuit not broken by the master isolating device

#### 1 connection - 4 wires - 2 entries/2 outlets

- Colour : Grey
- Nominal cross-section : 4 mm<sup>2</sup>
- Capacity - Rigid wire : 0.5 to 6 mm<sup>2</sup>
- Capacity – Flexible wire : 0.5 to 4 mm<sup>2</sup>
- Flexible wire with ferrule : 0.5 to 2.5 mm<sup>2</sup>
- Pitch : 5 mm

### General characteristics

#### Viking™ 3 terminal blocks with spring connection - for copper cables

- Screwless connection system, stainless steel spring type
- Used to make the electrical connection between 2 rigid copper wires, or flexible copper wires with or without ferrules
- Direct tool-free insertion of a rigid wire or flexible wire with ferrule, up to 6 mm pitch
- 2 areas for automatic insertion bridging combs (upper level only for 2-level blocks)
- For rails depth 15 mm, EN 60715 depth 7.5 mm and 15 mm

### Documentation

#### Catalogue pages & additional information

- [Selection chart \(p.326-327\)](#)
- [Description page \(p.330\)](#)
- [Technical page \(p.336\)](#)
- [Viking™ 3 terminal blocks with spring connection](#)

#### Agreements & certificates of conformity

- UL recogn - 20100921-E60900
- Ex - 002/F
- NF App Industri - NF208\_1012
- IMQ - CA02.04198
- VERITAS (BV) - 23393/BO BV
- ATEX - LCIE 16 ATEX 3049U - 02

#### Installation & technical data

- F01007EN-02