

CAT. N° 4 166 40



## THERMAL OVERLOAD RELAY RTX<sup>3</sup> 40 - 0.1 TO 0.16 A - FOR CTX<sup>3</sup> 22 AND 40 - NON DIFF.

Pack (number of units)	1
Volume (dm <sup>3</sup> )	0,356
Weight (g)	175,00

### Product characteristics

#### Thermal overload relays

- Class 10A
- Integrated auxiliary contacts 1 NO + 1 NC

#### RTX<sup>3</sup> 40

- For CTX<sup>3</sup> 22 and 40
- With screw terminals
- Type standard
- Adjustment range - I min. : 0.1 A
- Adjustment range - I max. : 0.16 A

### General characteristics

#### Thermal relays RTX<sup>3</sup> - for CTX<sup>3</sup> 3-pole industrial contactors

- Thermal protection against overloads, long starting times and lasting stalling of the motor
- Differential type ensures a better protection in case of one phase failure thanks to faster tripping
- Conform to IEC 60 947-1, IEC 60 947-4-1

### Documentation

#### Catalogue pages & additional information

- [Description page \(p.192\)](#)
- [Technical page \(p.186-187\)](#)
- [Technical page \(p.196-197\)](#)
- [Thermal relays RTX<sup>3</sup> - screw type terminals](#)

#### Installation & technical data

- [F01992EN-02](#)

#### Installation instructions & related documents

- [F07229AB](#)