

CAT. N° 7 646 87



THERMOSTAT NILOÉ 230 V - IVORY

Pack (number of units)	1
Volume (dm ³)	0,593
Weight (g)	100,00

Product characteristics

Electronic room thermostat

- For direct radiant ceiling panels and underfloor heating
- Adjustment range: from 10 °C to 30 °C
- Frost protection 7 °C
- Adjustment precision: 0.5 °C
- 1 potential free N/O contact
- Switching capacity:
 - 8 A - 250 V~ - resistive circuit
 - 2 A - 250 V~ - inductive circuit
- Power supply: 230 V~ 50/60 Hz
- Adjustable brightness of LEDs
- Can be associated with a clock for comfort and eco mode
- Ivory

General characteristics

Niloé™ - shutter controls, keycard switches and thermostats

- Mechanisms supplied with cover plates and support frames in flow-pack
- To be equipped with plates
- Screw terminals
- Fixing with screws or claws (supplied)

Documentation

Catalogue pages & additional information

- [Description page \(p.532\)](#)

Installation & technical data

- [F02163EN/00](#)

Installation instructions & related documents

- [LE09397AA](#)