

CAT. N° 0 286 96



## TRIP FREE SWITCH DMX<sup>3</sup>-I 2500 - FIXED VERSION - 4P - 2500 A

Pack (number of units)	1
Volume (dm <sup>3</sup> )	192,421
Weight (g)	62 000,00

### Product characteristics

#### Fixed version

- Supplied with:
  - 4 auxiliary contacts: NO/NC
  - flat rear terminals for connection with bars
  - door sealing

#### DMX<sup>3</sup>-I 2500

- Frame 2500
- 4P
- In : 2500 A

### General characteristics

#### Trip free switches DMX<sup>3</sup>-I - from 1250 to 6300 A

- Conform to IEC 60947-3

### Documentation

#### Catalogue pages & additional information

- [Description page \(p.162\)](#)
- [DMX3 - frame 2500, 4000 & 6300](#)
- [DMX3 - electronic protection units](#)

#### Installation & technical data

- [Y2687H](#)
- [F01800EN/01](#)
- [Y2958H](#)

#### Installation instructions & related documents

- [Y2762C](#)

#### Agreements & certificates of conformity

- [OC / CB - 60529](#)