

CAT. N° 7 646 51



## TV SINGLE STAR SOCKET NILOÉ - 9.5 MALE - ATTENUATION 1 DB - IVORY

Pack (number of units)	10
Volume (dm <sup>3</sup> )	3,762
Weight (g)	755,00

### Product characteristics

#### Single TV star sockets

- Low attenuation: 1 dB

#### TV - 9.5 male

- Ivory

### General characteristics

#### Niloé™ - television star sockets

- Mechanisms supplied with cover plates and support frames. To be equipped with plates. Fixing with screws or claws (supplied)
- For DVBT, Cablecast and satellite installation. UHD TV compatible. Class A shielded star sockets LTE Ready (4G protected).
- Recommended coaxial cable: 17 VATC. Star cabling (1 socket = 1 cable to antenna, splitter or multiswitch). Visual checking of the connection
- Meet EN 50083-4 and EN 50083-2 European directive. Low attenuation: less than 1 dB
- TV: male connector (Ø9.5 mm)
- R: female connector (Ø9.5 mm)
- SAT: "F type" connector
- TV: 5-68 / 120-862 MHz
- R: 87.5-108 MHz
- SAT: 950-2400 MHz

### Documentation



#### Catalogue pages & additional information

- [Description page \(p.535\)](#)



#### Installation & technical data

- [S000093616EN-00](#)



#### Installation instructions & related documents

- [LE08364AA](#)