

REF . 7 520 06


TWO-WAY SWITCH VALENA IN'MATIC - 10 AX 250 V~


Emballage (nombre number of units)	10
Volume (dm ³)	3,802
Poids (g)	725,00

Caractéristiques du produit
Switches 10 AX - 250 V~
Two-way switch

- Automatic terminals
- Becomes illuminated with LED Cat.No 0 676 86 or 7 520 57 (surround lighting in Valena Allure range)

Caractéristiques générales
Valena™ IN'MATIC mechanisms - switches

- Valena In'Matic mechanisms are supplied with metal support, for claw or screw mounting
- Supplied with mounted dust protection transparent shield
- To be equipped with Valena Life or Valena Allure cover plates and plates
- Packaged in boxes

Documentation associée
 **Catalogue pages & additional information**

- [Description page \(p.494\)](#)
- [Selection chart \(p.508\)](#)
- [Selection chart \(p.512\)](#)

 **Installation & technical data**

- [F02081FR/00](#)
- [F02081EN/00](#)

 **Installation instructions & related documents**

- [LE09162AD](#)

 **Agreements & certificates of conformity**

- [NF - NF012_1596](#)
- [VDE - 40044639](#)
- [OC / CB - FR_703340](#)