

CAT. N° 0 365 77

**VENTILATION GLAND - IP66 - IK08 - DRILLING \varnothing 40.5 MM**

| | |
|---------------------------|----------|
| Pack (number of units) | 24 |
| Volume (dm ³) | 20,72 |
| Weight (g) | 3 008,00 |

Product characteristics**Natural ventilation****IP 66 - IK 08 ventilation glands for cabinets**

- Polyamide PA 6 - RAL 7035
- Drilling \varnothing 40.5 mm

General characteristics**Heat regulation for cabinets and enclosures - ventilators****Documentation****Catalogue pages & additional information**

- [Description page \(p.313\)](#)
- [Heat regulation for cabinets and enclosures](#)