

CAT. N° 0 348 51



VENTILATOR WITH PLASTIC LOUVRE - IP54 - IK08 - 120/160 M³/H - RAL 7035

Pack (number of units)	1
Volume (dm ³)	12,618
Weight (g)	1 747,00

Product characteristics

Ventilators with plastic louvre

- IP 54 - IK 08
- 230 V - 50/60 Hz
- RAL 7035
- Equipped with finger-guard grilles
- Reduced external dimensions (7 to 10 mm)
- Ventilator is mounted on the outside of the enclosure or cabinet
- Screw fixing on a panel width 1 to 4 mm
- A second outlet louvre can be installed to increase the flow rate and optimise discharge rates from the enclosure

120/160 m³/h

- 120 m³ installed with filter
- 130 m³ with second louvre Cat.No 0 348 35
- 160 m³ for free blow out
- Supplied with a pair of louvres 250 x 250 mm
- Media filter washable G3, acc. EN 779

General characteristics

Heat regulation for cabinets and enclosures - ventilators

Documentation

Catalogue pages & additional information

- [Description page \(p.312\)](#)
- [Heat regulation for cabinets and enclosures](#)

Installation instructions & related documents

- [04168600/B](#)