

CAT. N° 0 608 94



## WEATHERPROOF LED PORTABLE SAFETY LAMP - SPECIALLY DESIGNED FOR SAFETY INTERVENTIONS IN ELECTRICAL ROOMS

Pack (number of units)	1
Volume (dm <sup>3</sup> )	5,081
Weight (g)	859,00

### Product characteristics

#### LED portable safety lamps

##### Weatherproof LED portable safety lamp

- Specially designed for safety interventions in electrical rooms
- 120° rotating handle
- 2 operating modes:
  - automatic changeover to emergency lighting when mains supply interruption
  - manual switching of emergency lighting after mains supply interruption
- Manual selection of lighting mode on push-button:
  - full power illumination 100 lumens / 1h duration
  - half power illumination 45 lumens / 3h duration
- flashing
- OFF
- 2 installation modes with docking station: wall-mounting or freestanding
- Magnetic fixing system on the back of the lamp
- Locating flashing LED when black-out
- Electronic anti-theft function
- Ni-Cd built-in battery pack
- IP 55 - IK 08
- Power supply (for docking station): 230 V +/- 10% - 50/60 Hz
- Low power consumption: 1.3 W
- Class III (lamp only)
- Plug-in terminal block for fixed power supply wiring
- Also delivered with AC power cord

### General characteristics

#### LED portable lamps

### Documentation



#### Catalogue pages & additional information

- [Description page \(p.689\)](#)