

CAT. N° 0 897 51



RECEPTACLE FOR FLOOR SOCKET ARTEOR/MOSAIC - ROUND VERSION - BRUSHED BROWN STEEL

Pack (number of units)	1
Volume (dm ³)	O/R
Weight (g)	O/R

Product characteristics

Receptacles for floor sockets

- Extra slim plate IP 44 - IK 08
- Equipped with a 180° opening flap
- Extra flat finish: thickness 2 mm
- Lighting base of receptacle by white LED
- To be equipped with 2 modules square version Arteor or Mosaic functions:
 - socket outlets without cover, German, Euro-US, Swiss, Danish, Israeli and French standards
 - Double USB chargers
 - RJ 11 and RJ 12 sockets, Television sockets
 - RJ 45 sockets UTP, FTP and STP without controlled access
 - loudspeaker sockets, HDMI sockets, HD 15 sockets without jack

Round receptacle

- Brushed brown steel

General characteristics

Floor sockets

Documentation

Catalogue pages & additional information

- [Description page \(p.479\)](#)

Installation & technical data

- [F01511EN/06](#)

Installation instructions & related documents

- [LE04522AD](#)