

CAT. N° 4 159 28



## DX<sup>3</sup> STOP ARC 6000 WITH BOTTOM SIDE SUPPLY - 1P+N ON RIGHT-HAND SIDE 230 V~ - 6A - 2 MODULES - C CURVE

Pack (number of units)	1
Volume (dm <sup>3</sup> )	0,369
Weight (g)	207,00

### Product characteristics

#### Arc fault detection circuit breakers

- Breaking capacity:
- 6000 - EN/IEC 60898 - 230/240 V~
- Compatible with prong-type supply busbars

#### Single pole + neutral 230 V~

- Neutral on right-hand side
- Nominal rating I<sub>n</sub> : 6 A
- Number of modules : 2

### General characteristics

#### DX<sup>3</sup> Stop Arc - bottom side supply - arc fault detection devices from 10 to 20 A

- Conform to IEC/EN 62606
- Can be equipped with DX<sup>3</sup> signalling and remote tripping auxiliaries
- Specific use: fire prevention by arc detection

### Documentation



#### Catalogue pages & additional information

- [Description page \(p.063\)](#)



#### Installation & technical data

- [F02541EN-02](#)