

Product sheet



VALENA LIFE LEGRAND

Push-dimmer without neutral Valena In'Matic - 240 V~
- 50 Hz

REF. 752062 | EAN. 3414970465214



> [Visit e-catalogue](#)

Product characteristics

- Valena™ IN'MATIC mechanisms - dimmers - Valena In'Matic mechanisms are supplied with metal support, for claw or screw mounting - To be equipped with Valena Life or Valena Allure cover plates and plates - Supplied with mounted dust protection transparent shield - Packaged in boxes
- Dimmers 240 V~ - 50 Hz - Equipped with overvoltage and short-circuit protection - When switched on, light up at the level set before last switch-off - Can be remotely controlled via non-illuminated pushbuttons (Cat.No 7 520 11), with each push-button able to perform the ON/OFF and dimming function - Screw terminalsPush-dimmer without neutral - For all types of lamps: - - dimmable LEDs: 5 W to 75 W (10 lamps max.) - dimmable compact fluorescent lamps: 5 W to 75 W (10 lamps max.) - halogen with ferromagnetic or electronic transformer: 3 VA to 400 VA - fluorescent tube ballast: 3 VA to 200 VA - halogen and incandescent 240 VA: 3 W to 400 W - When switched on, gradually (2 seconds) lights up at the level set before last switch-off - Functioning: - - dimming mode - pre-set level mode (0%, 33%, 66%, 100%) - nightlight mode: dimming down of the lamp for 1 hour

Documentation

TECHNICAL DOCUMENTATION

- [LE08593AA_imp.pdf](#) | PDF (0.21Mo)
- [LE07434AB_hermes.pdf](#) | PDF (0.57Mo)
-  [F01602FR-06.pdf](#) | PDF (0.88Mo)
-  [F01602EN-06.pdf](#) | PDF (0.79Mo)

CAD & Design specs / BIM

-  [752062_AllCATPart.stp](#) | IFC (14.14Mo)