

Product sheet



MOSAIC™ LEGRAND

Mosaic™ - 2-way pull-cord switch - 10 AX - 230 V~ - up to 2300 W - 2 modules -white

REF. 077014 | EAN. 3245060770143

[> Visit e-catalogue](#)

Product characteristics

- Mosaic™ Programme mechanisms - pull - cord switches and ventilation control - All two - way switches with indicator have a terminal for neutral connection and must be equipped with an indicator
- Pull - cord switches - Fast connection via automatic terminals, no tool requiredTwo - way switch, 10 AX - 2 modules - For controlling 230 V~ incandescent and halogen lamps up to 2300 W - White

Documentation

TECHNICAL DOCUMENTATION

→ LE10538AA.pdf | PDF (0.35Mo)

📄 F02937FR-01.pdf | PDF (0.14Mo)

📄 F02937EN-01.pdf | PDF (0.15Mo)

CAD & Design specs / BIM

BIM-LEGRAND-MOSAIC-2025-12-FRANCAIS.rvt | RVT (125.57Mo)

BIM-LEGRAND-MOSAIC-2025-FRANCAIS.rvt | RVT (124.38Mo)

📄 3D_LG-077014.stp | IFC (6Mo)

BIM-LEGRAND-MOSAIC-2025-12-ENGLISH.rvt | RVT (127.11Mo)

BIM-LEGRAND-MOSAIC-2025-ENGLISH.rvt | RVT (125.73Mo)

CATALOGUE PAGE & OTHERS

📄 ex223001_1174.pdf | PDF (0.07Mo)

Agreements & Certificates

📄 NF App Domestic-NF012_2275/A2 | (0.96Mo)

📄 OC / CB-FR_707532/M1 | (1.51Mo)