

Product sheet



LCS³ LEGRAND

LCS³ 19" PDU 1U 8 x 2P+E german standard with 3m power supply cord and equipped with a luminous switch

REF. 646823 | EAN. 3414970765468

PDU 19 inches 1U with 8 x 2P+E german standard outlets, to supply power to equipment in 19 inches enclosures. Comprises an aluminium casing, socket modules, a mounting solution and a termination solution.

> [Visit e-catalogue](#)

Description

PDU 19 inches 1U with 8 x 2P+E german standard outlets, to supply power to equipment in 19 inches enclosures. Comprises an aluminium casing, socket modules, a mounting solution and a termination solution.

Product characteristics

- Single phase
- 8 x 2P+E german standard outlets equipped with protective shutters
- Input voltage 230V
- Input current 16A
- Maximum power 3.7kW

The product's benefits

Installation

- Quick fixing (no screws) on 19 inches fixing centers. Can also be installed vertically by reverting the brackets (no screws).

Usage

- The LED switch is used to control the PDU power supply : a white LED is lit when the PDU sockets are supplied with power.

Advantages

- Angle of outlets is 55°

Documentation

TECHNICAL DOCUMENTATION

 S000093176EN-15.pdf | PDF (3.09Mo)

 S000093176FR-15.pdf | PDF (3.1Mo)

Agreements & Certificates

 LGRP-00707-V01.01-EN.pdf | PDF (0.62Mo)

CATALOGUE PAGE & OTHERS

 ex223001_1015.pdf | PDF (0.13Mo)