

# Product sheet



## LEGRAND

Standard luminaires U34 LED - 1h duration with opal diffuser - 450 lm

REF. 661180 | EAN. 3245066611808

> [Visit e-catalogue](#)

## Product characteristics

- U34LED environment friendly - indoor self - contained emergency lighting luminaires LED - LED Maintained/non-maintained units - High power LEDs with specially designed lenses optimizing the lighting distribution - IP 42 - IK 07 - Class II - Power supply : 230 V  $\pm$  10% - 50/60 Hz - Very low consumption switching power supply - Fully recyclable after removing - Environment friendly Ni - MH batteries - Removable plug - in plate to ease installation and maintenance - Automatic terminals with high capacity : 2 x 2.5 mm <sup>2</sup> - Charge monitor with a green LED - Can be equipped with metallic protection grids Cat.Nos 0 626 92/93
- Standard luminaires - Maintained/non-maintained (M/NM) - Standard luminaires incorporate an external manual lamp test with testing tool Cat.No 6 612 991 h duration with transparent diffuser - 450 lm - 1h (LEDs)

## Documentation

### TECHNICAL DOCUMENTATION

- [LE04859AB.pdf](#) | PDF (1.77Mo)
-  [S000082232FR-2.pdf](#) | PDF (8.01Mo)

### Agreements & Certificates

-  [LGRP-2015-295-V1-EN.pdf](#) | PDF (0.61Mo)

### CATALOGUE PAGE & OTHERS

-  [Legrand 661180 U34LED 450LM-1H M.zip](#) | ZIP
-  [ex223001\\_0908.pdf](#) | PDF (0.06Mo)