

# Product sheet



## LEGRAND

Emergency luminaire URA ONE - standard Non maintained - 1h - 100 lm - LED

REF. 661621 | EAN. 3414970312174

> [Visit e-catalogue](#)

## Product characteristics

- URA ONE - indoor self - contained emergency lighting luminaire LED - LED non-maintained and maintained units - Certified to IEC and EN 60598 - 2 - 22 standards - High power LEDs with optimized lighting distribution - Low consumption switching power supply. Fully recyclable - Plug - in back with pre - cutted holes grid to ease installation and maintenance - Automatic terminals with high capacity : 2 x 2.5mm<sup>2</sup>. IP 42 - IK 07 - Duration : 1 and 3 hours. Ni - Cd or Ni - MH batteries. Recharge time : 24 hours. Charge monitor with a green LED. Opal diffuser - Power supply : 230 V~ ± 10% - 50/60 Hz. Class II - Flat flush-mounting integration into ceiling and wall with flush-mounting frame Cat.Nos 6 616 50/51 - Decorative frame to enhance surface - mounting aesthetic integration Cat.Nos 6 616 54/55
- Standard luminaires - Require normal lighting manual switching off in order test emergency lighting non-maintained - 100 lm - 1h (LEDs)

## Documentation

### TECHNICAL DOCUMENTATION

- LE07121AF.pdf | PDF (0.83Mo)
- 📄 S000083576FR-3.pdf | PDF (3.97Mo)
- 📄 S000083576EN\_3.pdf | PDF (4.07Mo)

### CAD & Design specs / BIM

Legrand\_Emergencia\_URA\_ONE\_EXPORT\_EN.rfa | RFA (1.74Mo)

### CATALOGUE PAGE & OTHERS

- 📖 ex223001\_0907.pdf | PDF (0.06Mo)
- ⚙️ Legrand 661621 URAONE 100LM-1H NM.zip | ZIP
- 📖 ex223001\_0906.pdf | PDF (0.09Mo)

### Agreements & Certificates

- 📄 AENOR S-007/000004 | (0.91Mo)
- 📄 LGRP-00533-V01.01-EN.pdf | PDF (0.69Mo)