

Product sheet



LEGRAND

Emergency luminaire URA ONE - standard
Maintained/Non maintained - 1h - 100 lm - LED

REF. 661631 | EAN. 3414970312211

> [Visit e-catalogue](#)

Product characteristics

- URA ONE - indoor self - contained emergency lighting luminaire LED - LED non-maintained and maintained units - Certified to IEC and EN 60598 - 2 - 22 standards - High power LEDs with optimized lighting distribution - Low consumption switching power supply. Fully recyclable - Plug - in back with pre - cutted holes grid to ease installation and maintenance - Automatic terminals with high capacity : 2 x 2.5mm². IP 42 - IK 07 - Duration : 1 and 3 hours. Ni - Cd or Ni - MH batteries. Recharge time : 24 hours. Charge monitor with a green LED. Opal diffuser - Power supply : 230 V~ ± 10% - 50/60 Hz. Class II - Flat flush-mounting integration into ceiling and wall with flush-mounting frame Cat.Nos 6 616 50/51 - Decorative frame to enhance surface - mounting aesthetic integration Cat.Nos 6 616 54/55
- Standard luminaires - Require normal lighting manual switching off in order test emergency lighting Maintained/non-maintained (M/NM) - Can also operate in non-maintained mode according to the wiring of normal lighting - 100 lm - 1h (LEDs)

Documentation

TECHNICAL DOCUMENTATION

- LE06557AF.pdf | PDF (1.85Mo)
- 📄 S000083576FR-3.pdf | PDF (3.97Mo)
- 📄 S000083576EN_3.pdf | PDF (4.07Mo)

CAD & Design specs / BIM

Legrand_Emergencia_URA_ONE_EXPORT_EN.rfa | RFA (1.74Mo)

CATALOGUE PAGE & OTHERS

- 📖 ex223001_0907.pdf | PDF (0.06Mo)
- ⚙️ Legrand 661631 URAONE 100LM-1H M.zip | ZIP
- 📖 ex223001_0906.pdf | PDF (0.09Mo)

Agreements & Certificates

- 📄 LGRP-00660-V01.01-EN.pdf | PDF (0.61Mo)
- 📄 ENEC-ENEC/000994 | (0.5Mo)
- 📄 AENOR-007/001689 | (0.39Mo)