

Product sheet



LEGRAND

Emergency luminaire URA ONE - standard
Maintained/Non maintained - 1h - 200 lm - LED

REF. 661633 | EAN. 3414970312259

[> Visit e-catalogue](#)

Product characteristics

- URA ONE - indoor self - contained emergency lighting luminaire LED - LED non-maintained and maintained units - Certified to IEC and EN 60598 - 2 - 22 standards - High power LEDs with optimized lighting distribution - Low consumption switching power supply. Fully recyclable - Plug - in back with pre - cutted holes grid to ease installation and maintenance - Automatic terminals with high capacity : 2 x 2.5mm². IP 42 - IK 07 - Duration : 1 and 3 hours. Ni - Cd or Ni - MH batteries. Recharge time : 24 hours. Charge monitor with a green LED. Opal diffuser - Power supply : 230 V~ ± 10% - 50/60 Hz. Class II - Flat flush-mounting integration into ceiling and wall with flush-mounting frame Cat.Nos 6 616 50/51 - Decorative frame to enhance surface - mounting aesthetic integration Cat.Nos 6 616 54/55
- Standard luminaires - Require normal lighting manual switching off in order test emergency lighting Maintained/non-maintained (M/NM) - Can also operate in non-maintained mode according to the wiring of normal lighting - 200 lm - 1h (LEDs)

Documentation

TECHNICAL DOCUMENTATION

- [LE06557AF.pdf](#) | PDF (1.85Mo)
- [S000083576FR-3.pdf](#) | PDF (3.97Mo)
- [S000083576EN_3.pdf](#) | PDF (4.07Mo)

CAD & Design specs / BIM

- [Legrand_Emergencia_URA_ONE_EXPORT_EN.rfa](#) | RFA (1.74Mo)

CATALOGUE PAGE & OTHERS

- [ex223001_0907.pdf](#) | PDF (0.06Mo)
- [Legrand 661633 URAONE 200LM-1H M.zip](#) | ZIP
- [ex223001_0906.pdf](#) | PDF (0.09Mo)

Agreements & Certificates

- [AENOR S-007/000004](#) | (0.91Mo)
- [LGRP-00660-V01.01-EN.pdf](#) | PDF (0.61Mo)
- [ENEC-ENEC/000994](#) | (0.48Mo)
- [AENOR-007/001689](#) | (0.9Mo)