

Product sheet



LEGRAND

Emergency shutdown control device -2 NO/NC + 2 lights -5 A -24 V= -RAL 9003

REF. 138074 | EAN. 3414970520593

> [Visit e-catalogue](#)

Product characteristics

- Safety boxes 90 series - for fire detection and fire alarm system, emergency exit, extinguishing system, remote switching
- Manual call points (MCP) - IP 30 - IK 07 - Surface - mounting or flush-mounting (IP 30) - Dimensions : 90x90x57 mm (surface - mounting with its base) or 90x90x24 mm (flush-mounting with flush boxes for wiring devices - drilling diameter 67 mm - for 60 mm Fixing centres) - Can be fitted on trunking Cat. Nos 0 104 63/64, 35x105 mm or 50x105 mm, with the universal support Cat. No 0 109 13 - Call by pressing the membrane (pressure 2.5 kg) with clear display of the call position - Reset on Front of device, with special key Cat. No 0 380 38 (supplied with the product) - Possibility to add an optional mechanical status indicator Cat. No 1 380 93 to provide additional signalling - Can receive a sealable cover Cat.No 0 380 97 Emergency shutdown control devices - Color of the mechanical enclosure : white RAL 9003 - Emergency shutdown control device - 2 contacts with indicator light - Equipped with 2 NO/NC contacts 5A 24V DC - Equipped with 2 indicator lights (1 red LED + 1 green LED) 230 V free signalling wiring - Can be used to trigger a technical alarm - 2 LEDs in Front indicating the change of status of the controlled equipment

Documentation

TECHNICAL DOCUMENTATION

→ [LE07339AB.pdf](#) | PDF (1.91Mo)

CATALOGUE PAGE & OTHERS

 [ex223001_0919.pdf](#) | PDF (0.07Mo)