

Product sheet



LEGRAND

Rotating and fixable multi-outlet extension 4 sockets with surge protection cable 1,5m and 1,5mm² section

REF. 694507 | EAN. 3414971944367

> [Visit e-catalogue](#)

Product characteristics

- Multi-outlet extension with 4 flush 2P+T sockets with Schuko standard, 16A, 230V, 3680W. multi-outlet extension swivelling every 12° to the right or left compared to a horizontal installation.
- Multi-outlet extension with surge protection. Operation : green light, the multi-outlet extension is protected. With the light off, the surge protection is no longer functional. However, the sockets and USB ports are powered. If the surge protection function is necessary for you, you must in this case change the multi-outlet extension.
- One 90° socket to connect a transformer without blocking another socket. Other sockets being oriented at 45°
- Blue illuminated ON / Off switch. Bi-colour Multi-outlet extension: white and black / dark grey

Recommendation / Restriction

- Indoor use

The product's benefits

Installation

- Multi-outlet extension with several installation possibilities.

Usage

- 3 installation possibilities: - product fixed to the wall (by screws not supplied) - product fixed by a cable tie (not supplied) - placed product

Avantages

- New: Multi-outlet extensions are fitted with flush sockets, thus ensuring an aesthetic product and preventing dirt from getting on the wells.
- Multi-outlet extension swivelling every 12° to the right or left compared to a horizontal installation.

Documentation

TECHNICAL DOCUMENTATION


 F03121EN-00.pdf | PDF (0.23Mo)


 F03121FR-00.pdf | PDF (0.23Mo)

Agreements & Certificates

 MEEI-UP 69265087 | (1.06Mo)

 LGRP-02080-V01.01-EN.pdf | PDF (0.8Mo)

 OC / CB-FR_710045/M1 | (0.88Mo)

 SNI-PCS 01223.01 | (1.29Mo)

CATALOGUE PAGE & OTHERS

 ex223001_0831.pdf | PDF (0.17Mo)

