

Product sheet



LEGRAND

Multi-outlet 4 socket outlets cable 1.5m and 1.5mm² section

REF. 694554 | EAN. 3414971945302

> [Visit e-catalogue](#)

Product characteristics

- Multi-outlet 4 socket outlets German standard, 16A, 230V, 3680W
- 1 socket outlet is at 90° to plug a transfo without condemning another outlet
- PP material
- White PVC cable 1,5M, 3x1,5mm²

Recommendation / Restriction

- Indoor use

The product's benefits

Installation

- Multi-outlet to be placed on a table, on the floor...

Usage

- Universal product for indoor use

Advantages

- Extra-slim multi-outlet
- 1 socket outlet is at 90° to plug a transfo without condemning another outlet

Documentation

TECHNICAL DOCUMENTATION

 F03276FR-00.pdf | PDF (0.18Mo)

 F03276EN-00.pdf | PDF (0.2Mo)

Agreements & Certificates

 LGRP-02052-V01.01-EN.pdf | PDF (0.86Mo)

 MEEI-UP 69262707 | (1.33Mo)

 OC / CB-FR_708406 | (0.54Mo)

 SNI-PCS 01223.01 | (1.29Mo)

CATALOGUE PAGE & OTHERS

 ex223001_0835.pdf | PDF (0.15Mo)