

Product sheet



LEGRAND

Multifunction remote control dimmer - dimmable LEDs and CFLs - DIN 1 module

REF. 002671 | EAN. 3414970520371

> [Visit e-catalogue](#)

Product characteristics

- Compatible with energy saving lamps : dimmable LEDs and CFLs (Compact Fluorescent Lamps)
- Load : 1 to 75 W dimmable LEDs 1 to 100 W dimmable CFL 1 to 300 VA dimmable fluorescent tubes 1 to 200 VA dimmable LED / halogen lamps with ferromagnetic transformer 1 to 200 VA dimmable LED / halogen lamps with electronic transformer 1 to 300 W halogen and incandescent lamps
- Mains voltage 230VAC - 50/60Hz
- DIN 1 module
- Power consumption in standby mode: 0.1 W

Recommendation / Restriction

- Legrand Close UP application needs to be associated with the configuration gateway Cat.No. 0 882 40

The product's benefits

Installation

- 5 manually programmable functions accessible directly from the device and 3 additional functions accessible via Legrand Close UP application only

Usage

- 5 manually programmable functions: dimmer with level memory, dimmer without level memory, latching relay, timer, dual threshold timer + 3 additional functions: child room fading, timer with switch-off warning function, dimming at preset levels

Advantages

- Can replace a pre-installed dimmer
- Actuator or timer controlled by pushbuttons

Documentation

TECHNICAL DOCUMENTATION

- [LE08218AD.pdf](#) | PDF (1.68Mo)
-  [S000090635FR-4.pdf](#) | PDF (3.16Mo)
-  [S000090635EN-4.pdf](#) | PDF (3.16Mo)

CAD & Design specs / BIM

-  [002671.dwg](#) | DWG (0.11Mo)

CATALOGUE PAGE & OTHERS

-  [ex223001_0108.pdf](#) | PDF (0.08Mo)