

# Product sheet



## LEGRAND

### KNX controller dimming 1-10v din 10 outputs

REF. 002668 | EAN. 3414972052283

> [Visit e-catalogue](#)

## Product characteristics

- 10 outputs - switching 16A & dimming 1 - 10V (4000VA max)
- DIN 10 modules
- Mains voltage 230VAC - 50/60Hz
- Power supply from KNX bus ( 10mA)

## Recommendation / Restriction

- Configuration through ETS tool from KNX association

## The product's benefits

### Installation

- Connected with the BUS/KNX cable

### Usage

- Each channel can actualize any of these functions separately: staircase, scene, operating hour, forced operation

### Avantages

- Because a broad range of KNX devices communicate with each other, (even if they are from different manufacturer) KNX technology answers to high demands for smart home or building thanks to endless flexibility and personalization
- Configurable behaviour after voltage return, voltage failure or ETS download
- Manual operation feature for each channel using membrane switches

## Documentation

### TECHNICAL DOCUMENTATION

S000114126EN-1.pdf | PDF (0.31Mo)

S000114126FR\_1.pdf | PDF (0.3Mo)

LE12365AC.pdf | PDF (0.32Mo)

### Agreements & Certificates

KNX EIB-11/16742/20 | (0.79Mo)

### CATALOGUE PAGE & OTHERS

ex223001\_0896.pdf | PDF (0.07Mo)

### Software & configurators

LOG\_RA00196AA\_002668 - V01.01.zip | ZIP (0.11Mo)

