

Product sheet



LEGRAND

HRC cartridge fuse - cylindrical type gG 10 x 38 - 25 A
- without indicator

REF. 013325 | EAN. 3245060133252

> [Visit e-catalogue](#)

Product characteristics

- HRC cartridge fuses
- Cylindrical type gG - Conform to EN 60269 - 1, IEC 60269 - 1 and 210 x 38 HRC - Without indicator - Rating : 25 Amps - Voltage ~ : 500 Volts - Rupture capacity : 100000 Amps

Documentation

TECHNICAL DOCUMENTATION

 F00192EN-10.pdf | PDF (1.54Mo)

 F00192FR-10.pdf | PDF (1.54Mo)

Agreements & Certificates

 LGRP-2015-225-v1-fr.pdf | PDF (0.6Mo)

CATALOGUE PAGE & OTHERS

 ex223001_0263.pdf | PDF (0.05Mo)

 ex223001_0261.pdf | PDF (0.1Mo)

 ex223001_0264.pdf | PDF (0.05Mo)