

Product sheet



LEGRAND

Cartridge fuse 10 x 38 mm - type gG - without indicator
- 2 A

REF. 013302 | EAN. 3245060133023

> [Visit e-catalogue](#)

Product characteristics

- Rupture capacity 100000 A - Rated voltage 500V~
- Dimension 10 x 38 mm.
- Ceramic body and silver - plated contacts
- Conform to IEC/EN 60269-1 and 2, NFC 60-200.

The product's benefits

Installation

- Compatible with Legrand fuse carriers SP 38.

Documentation

TECHNICAL DOCUMENTATION



F00192EN-10.pdf | PDF (1.54Mo)



F00192FR-10.pdf | PDF (1.54Mo)

Agreements & Certificates



LGRP-2015-225-v1-fr.pdf | PDF (0.6Mo)

CATALOGUE PAGE & OTHERS



ex223001_0263.pdf | PDF (0.05Mo)



ex223001_0261.pdf | PDF (0.1Mo)



ex223001_0264.pdf | PDF (0.05Mo)