

Product sheet



LEGRAND

HRC cartridge fuse - cylindrical type aMM 14 X 51 - 25 A - with indicator

REF. 014125 | EAN. 3245060141257

> [Visit e-catalogue](#)

Product characteristics

- HRC cartridge fuses
- Cylindrical type aM (motor rated) - Conform to EN 60269 - 1, IEC 60269 - 1 and 214 x 51 HRC - With striker - Rating : 25 Amps - Voltage ~ : 500 Volts - Rupture capacity : 100000 Amps

Documentation

TECHNICAL DOCUMENTATION

-  F00188EN-08.pdf | PDF (2.04Mo)
-  F00188FR-08.pdf | PDF (2.08Mo)

CATALOGUE PAGE & OTHERS

-  ex223001_0263.pdf | PDF (0.05Mo)
-  ex223001_0261.pdf | PDF (0.1Mo)
-  ex223001_0264.pdf | PDF (0.05Mo)