

# Product sheet



## LEGRAND

Cartridge fuse 14 x 51 mm - type gG - with stricker - 32 A

REF. 014532 | EAN. 3245060145323

[> Visit e-catalogue](#)

## Product characteristics

- Rupture capacity 100000 A - Rated voltage 500V~
- Dimension 14 x 51 mm.
- Ceramic body and silver - plated contacts
- With stricker to display the fuse status (operational / blown).
- Conform to IEC/EN 60269-1 and 2, NFC 60-200.

## The product's benefits

### Installation

- Compatible with Legrand fuse carriers SP 51 equipped with micro-switch.

## Documentation

### TECHNICAL DOCUMENTATION

F00192EN-10.pdf | PDF (1.54Mo)

F00192FR-10.pdf | PDF (1.54Mo)

### CATALOGUE PAGE & OTHERS

ex223001\_0263.pdf | PDF (0.05Mo)

ex223001\_0261.pdf | PDF (0.1Mo)

ex223001\_0264.pdf | PDF (0.05Mo)