

Product sheet



LEGRAND

Fuse carrier 1P+N for cartridge fuses 10.3 x 38 mm - 32A

REF. 005824 | EAN. 3245060058241

> [Visit e-catalogue](#)

Product characteristics

- With insulated carrier class II, padlockable with Accessory 005799
- Terminals capacity 1 x 16 mm² maxi, IP 2X, screw head PZ1
- Conform to EN 60269 - 1 and IEC 60269 - 1 - 3
- Possibility to signal indicator blown fuse with accessory 005790
- Fuse not supplied

Recommendation / Restriction

- This product should be installed in compliance with installation rules, preferably by a qualified electrician. Incorrect installation and/or incorrect use can lead to risk of electric shock or fire. Before carrying out the installation, read the instructions and take account of the product's specific mounting location. Do not open up, dismantle, alter or modify the device except where specifically required to do so by the instructions. All Legrand products must be opened and repaired exclusively by personnel trained and approved by Legrand. Any unauthorised opening or repair completely cancels all liabilities and the rights to replacement and guarantees. Use only Legrand brand accessories.

The product's benefits

Installation

- Fitted with two DIN rail clamps, one top side and one bottom side, allowing an independent removal of this product when the prong busbar supplying the row is still in place.

Usage

- Fitted with a label holder allowing a clear, visible and convenient identification of the circuit.

Documentation

TECHNICAL DOCUMENTATION

 [fa221bfr.pdf](#) | PDF (0.44Mo)

 [fa221ben.pdf](#) | PDF (0.45Mo)

CAD & Design specs / BIM

 [005818.dwg](#) | DWG (0.06Mo)

CATALOGUE PAGE & OTHERS

 [ex223001_0091.pdf](#) | PDF (0.09Mo)

Agreements & Certificates

 [LGRP-2015-149-V1-EN.pdf](#) | PDF (0.62Mo)

 [NF App Domestic-655175](#) | (0.14Mo)

