

Product sheet



LEGRAND

HRC blade type cartridge fuse - cylindrical type aM 22
X 58 - 50 A - w indicator

REF. 016050 | EAN. 3245060160500

> [Visit e-catalogue](#)

Product characteristics

- HRC blade type cartridge fuses - gG/gL and aM types
- Type aM (motor rated) - Conform to EN 60269 - 1, IEC 60269 - 1, 2 and VDE 0636 - 1 - Fully insulated end plate and handle lugs
- Size - With indicator - Rating : 125 Amps - Voltage ~ : 500 Volts - Breaking capacity : 120000 Amps

Documentation

TECHNICAL DOCUMENTATION



F00190EN-06.pdf | PDF (0.92Mo)



F00190FR-06.pdf | PDF (0.94Mo)

CATALOGUE PAGE & OTHERS



ex223001_0264.pdf | PDF (0.05Mo)