

Product sheet



LEGRAND

Cartridge fuse 22 x 58 mm - type gG - without stricker
- 50 A

REF. 015350 | EAN. 3245060153502

> [Visit e-catalogue](#)

Product characteristics

- Rupture capacity 100000 A - Rated voltage 500V~
- Dimension 22 x 58 mm.
- Ceramic body and silver - plated contacts
- Conform to IEC/EN 60269-1 and 2, NFC 60-200.

The product's benefits

Installation

- Compatible with Legrand fuse carriers SP 58.

Documentation

TECHNICAL DOCUMENTATION

 F00192EN-10.pdf | PDF (1.54Mo)

 F00192FR-10.pdf | PDF (1.54Mo)

Agreements & Certificates

 LGRP-2015-332-v1-fr.pdf | PDF (0.6Mo)

CATALOGUE PAGE & OTHERS

 ex223001_0263.pdf | PDF (0.05Mo)

 ex223001_0261.pdf | PDF (0.1Mo)

 ex223001_0264.pdf | PDF (0.05Mo)