

Product sheet



DLPLUS LEGRAND

DLPlus Mini-Trunking 1 compartment with a stop wire membrane, without separation partition, 40x20mm. White

REF. 030027 | EAN. 3245060300272

> [Visit e-catalogue](#)

Product characteristics

- Stop wire membrane allows to maintain cables inside the mini - trunking
- Delivered in length of 2,10m
- Comply with reliability, safety and technical performance requirements accord EN50085 - 2 - 1
- IP40: protected against solid bodies larger 1mm maximum. Shock resistance at 2 joules.

The product's benefits

Installation

- Fixing by: gluing (Neoprene glue (cat.no 030949), wall plug (cat.no 030898, 030899), DLP rapid wall plug (ref 0308 97) or screw, nails...

Usage

- Can be installed in tertiary and residential

Documentation

TECHNICAL DOCUMENTATION

 F00988EN-06.pdf | PDF (2.71Mo)

 F00988FR-04.pdf | PDF (2.59Mo)

Agreements & Certificates

 NF Conduits-NF 593021O | (0.08Mo)

 LGRP-01603-V02.01-EN.pdf | PDF (0.92Mo)

 LGRP-01603-V02.01-FR.pdf | PDF (0.88Mo)

CATALOGUE PAGE & OTHERS

 ex223001_1045.pdf | PDF (0.13Mo)

 ex223001_1048.pdf | PDF (0.04Mo)