

Product sheet



DLPLUS LEGRAND

Variable internal-external angle for DLPlus mini-trunking 40x20mm

REF. 030281 | EAN. 3245060302818

> [Visit e-catalogue](#)

Product characteristics

- Variable internal - external angle of 60 to 120 degrees
- Respect the protection index
- Improvement of aesthetics (covering of the cut)
- Colour: white

The product's benefits

Installation

- Clips directly on the body of the mini-trunking

Usage

- Allows a neat and clean electrical installation finish

Documentation

TECHNICAL DOCUMENTATION

→ 104870245-03.pdf | PDF (0.22Mo)

 F00988EN-06.pdf | PDF (2.71Mo)

 F00988FR-04.pdf | PDF (2.59Mo)

Agreements & Certificates

 LGRP-01603-V02.01-EN.pdf | PDF (0.92Mo)

 LGRP-01603-V02.01-FR.pdf | PDF (0.88Mo)

CATALOGUE PAGE & OTHERS

 ex223001_1045.pdf | PDF (0.13Mo)

 ex223001_1048.pdf | PDF (0.04Mo)