

Product sheet



LEGRAND

Junction box - IP 30 - IK 07 - 4P - cable section 35 mm² - 125 A

REF. 033044 | EAN. 3245060330446

> [Visit e-catalogue](#)

Product characteristics

- Connection- "Standard" distribution Junction boxes IP 30 - IK 07- For copper cables- 4 connections per pole- Reversible stirrup for zero clamping- Fitted with 4 or 5 junction blocks mounted on an insulated strip with a sheet steel cover- Knock-out entries for conduits Ø 9 and 21 mm- Sealable cover screws- Sealable cover screws - Poles : 4 - Cable section : 35 mm²- Rated current : 125 A

Documentation

TECHNICAL DOCUMENTATION

→ [041102-01.pdf](#) | PDF (0.07Mo)

CATALOGUE PAGE & OTHERS

 [ex223001_0303.pdf](#) | PDF (0.1Mo)