

Product sheet



LCS³ LEGRAND

Cable category 6A U/FTP 4 pairs LSZH Euroclass Cca
500 meters yellow

REF. 032884 | EAN. 3414971241541

This cat. 6A U/FTP 4 twisted pairs cable supports data transmission in a structured cabling system while protecting from electromagnetic interferences.

> [Visit e-catalogue](#)

Description

This cat. 6A U/FTP 4 twisted pairs cable supports data transmission in a structured cabling system while protecting from electromagnetic interferences.

Product characteristics

- Category 6A U/FTP : for up to 10 Gigabits per second data rate, shielded cable
- 4 twisted pairs cable
- Low Smoke Zero Halogen materials that emit limited smoke and no halogen when exposed to high sources of heat.
- Euroclass Cca offers good reaction to fire with lower flame propagation and heat release than ordinary Dca class.
- Power over Ethernet : 802.3 bt PoE++ applications compatible according to installation standards ISO/IEC 14763-2 (final draft) and EN 50174-2 : 2018

Recommendation / Restriction

- Compliant with ISO/IEC 11801 and ANSI/TIA 568 standards

Documentation

TECHNICAL DOCUMENTATION

 S000106471FR-04.pdf | PDF (0.12Mo)

 S000106471EN-04.pdf | PDF (0.12Mo)

Agreements & Certificates

 LGRP-01342-V01.01-EN.pdf | PDF (0.57Mo)

 LGRP-01411-V02.01-EN.pdf | PDF (0.84Mo)

 DOP-DOP O-CO_046-12220-C | (0.56Mo)

The product's benefits

Usage

- For the safety of people , Low Smoke Zero Halogen materials emit limited smoke and no halogen when exposed to high sources of heat. For the safety of goods, Euroclass Cca offers good reaction to fire with lower flame propagation and heat release than ordinary Dca class.

CATALOGUE PAGE & OTHERS

 ex223001_0980.pdf | PDF (0.07Mo)

 AoC-CL2_C6A_UFTP_32884_ac1191059 | (0.06Mo)

 AoC-PL2_C6A_UFTP_32884_ac1191058 | (0.06Mo)