

Product sheet



LEGRAND

Industrial box - plastic - IP55 - IK07 - opaque cover - 155x110x74 mm

REF. 035940 | EAN. 3245060359409

> [Visit e-catalogue](#)

Product characteristics

- Plastic industrial boxes - Smooth surfaces - Choice of Fixing : - Internal : 4 oblong holes at back of box - At the 4 corners outside the wiring space, with 4 screws - Using wall mounting lugs Cat.No 0 358 02 (except boxes 130 x 75 x 74 mm)
- IP 55 - IK 07 grey RAL 7035 - Class II provided by protective caps for the Fixing screws (supplied) - Equipment can be fixed on rail or solid plate - IP 2X terminal blocks fixed at the top from 130 x 130 mm size - Cover opened/closed with 1/4 turn of a flat screwdriver. Indication of closed/open position : I/O - Captive covers with ties, except boxes 310 x 240 mm and 360 x 270 mm - Opaque cover - Internal dimensions - Height x Width x Depth (mm) : 155 x 110 x 74

Documentation

TECHNICAL DOCUMENTATION

-  F00204FR-01.pdf | PDF (0.13Mo)
-  EXB22009_Flipbook_FR_(03_2022).pdf | PDF (6.2Mo)
-  F00204EN-01.pdf | PDF (0.16Mo)
-  EXB22010_Flipbook_EN_(03_2022).pdf | PDF (6.56Mo)

CATALOGUE PAGE & OTHERS

-  ex223001_0808.pdf | PDF (0.06Mo)
-  ex223001_0807.pdf | PDF (0.09Mo)