

Product sheet



LEGRAND

Roof ventilator - with motor - 1000 m³/h - IP23 - IK08 - RAL 7035

REF. 034808 | EAN. 3245060348083

> [Visit e-catalogue](#)

Product characteristics

- Heat regulation for cabinets and enclosures - ventilators
- Roof ventilators - Plastic - RAL 7035 - Provide very high extraction rate - Screw mounting on top of enclosures - Dimensions : 400 x 350 x 100 mm - Delivered without input air louvre - IP 23 - IK 08 - With motor - Free blowing : 1000 m³/h - Flow rate with 1 louvre Cat.No 0 348 35 : 400 m³/h - Flow rate with 2 louvres Cat.No 0 348 35 : 500 m³/h - Flow rate with 1 louvre Cat.No 0 348 36 : 500 m³/h - Flow rate with 2 louvres Cat.No 0 348 36 : 600 m³/h

Documentation

TECHNICAL DOCUMENTATION

→ [041395-00.pdf](#) | PDF (0.14Mo)

CATALOGUE PAGE & OTHERS

 [ex223001_0442.pdf](#) | PDF (0.09Mo)

 [ex223001_0441.pdf](#) | PDF (0.08Mo)